



Ortronics
Telecommunications Main Ground Bar
Part No. GB4X20TMGB



Manufactured of 1/4 in thick electrolytic tough pitch 110 alloy copper bar. Includes 1-1/2 in insulators and 1 in offset stainless steel mounting brackets. Includes one 1/2 oz. tube of antioxidant joint compound. Meets BICSI and ANSI/TIA-607 standards. Kits include: (1) Copper bonding bar with brackets and insulators, (6) #6 compression lugs, (3) #2 compression lugs, (1) 2/0 compression lug, (1) 4/0 compression lug, (12) 1/4 in-20 x 3/4 in SS hex head cap screw, (12) 1/4 in-20 SS lock washer, (12) 1/4 in-20 SS hex nut, (6) 3/8 in-16 x 1 in SS hex head cap screw, (6) 3/8 in-16 SS lock washer, (6) 3/8 in-16 SS hex nut.

Features & Benefits

Manufactured of 1/4" thick electrolytic tough pitch 110 alloy copper bar

Includes 1-1/2" insulators and 1" off-set stainless steel mounting brackets

Specifications

General Info

| | | | |
|-------------------|---------------|--------------------|--------------|
| Product Line | Ortronics | UPC Number | 662875665175 |
| Country Of Origin | United States | Application Sector | Commercial |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 20.0 in | Product Depth US | 3.0 in |
| Product Height US | 4.0 in | | |

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|