
6-LC (12 FIBERS) MULTIMODE AQUA ADAPTERS WITH CERAMIC ALIGNMENT SLEEVES

OR-OFP-LCD12LC | [Ortronics](#)



FEATURES & BENEFITS

The Ortronics OptiMo® OFP series adapter panels are used with our popular FC Series modular fiber cabinets, offering great flexibility in structured cabling design. Front-removable adapter panels are available with LC, SC, ST, and MT-RJ adapters and feature options ideal for both single mode and multimode applications.



PRODUCT
ENVIRONMENTAL PROFILE

- **Standard adapter panel is front removable:** Ideal for simple moves, adds, and changes.
- **Uses plunger/grommet fastener:** Holds adapter panels securely in place.

SPECIFICATIONS

GENERAL INFO

Color: Aqua
Number Of Ports: 6
Typical Applications: Multimode
Connection Type: LC
Installation Destination: Fiber Cabinets

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Height (Metric): 30 mm
Height (US): 1.19"
Width (Metric): 130 mm

CORD INFORMATION

Fiber Type:

TECHNICAL INFORMATION

Fiber Capacity: 12
Performance Rating: LC
Capacity: Standard Density
Equipment Type: Adapters

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

