



MatixGo

JW4012 - JG4012 - JB4012
JW4022 - JG4022 - JB4022

Switches with Key



Use


Key controls for lighting and other controls

Range

Designation	Item
1-Way switch 2P 10AX - 250Va.c. with key	☐ JW4012
- the key can be removed in both positions	☐ JG4012
- the keys are different for the various devices	☐ JB4012
1 module	
2-Way switch 1P 10AX - 250Va.c. with key	☐ JW4022
- the key can be removed in both positions	☐ JG4022
- the keys are different for the various devices	☐ JB4022
1 module	

Colors: ☐ White ☐ Grey ☐ Black

Overall dimensions (mm)



	A	B	C	D	E
..4012 - ..4022	45.1	22.5	44.1	7.6	9.9

Connection

Terminal type: screw clamp
Terminal capacity: 2 x 4 mm² max
Stripping length: 11 mm
Compatible with flexible or rigid cables

Technical characteristics

- **Protection index:**
(considering a complete installation, including cover plate)
 - Penetration by solid bodies/liquid: IP40
 - Impact test: IK04
- **Material characteristics:**
 - Case: PC (polycarbonate)
 - Key cover: PC/ABS
 - Halogen Free
 - UV resistant
 - Self-extinguishing:
 - 850° C / 30 s for insulating parts holding live parts in place
 - 650° C / 30 s for other parts made of insulating materials
- **Electrical characteristics**
Voltage: 250 V a.c.
Current: 10 AX
- **Climatic characteristics**
Storage temperature: - 10° C to + 70° C
Use temperature: - 5° C to + 35° C

Cleaning

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.
Caution: Always test before using special cleaning products.

Standard and approvals

Compliance with standards IEC/EN 60669-1.
Refer to e.catalogue.