


Pre-connected HDMI 2.0 connector



Use


HDMI sockets are used to transmit High Definition digital audio/video streams between a source (computer, DVD or Blu-Ray player, etc) and a compatible receiver (TV, video projector, etc). To ensure a high-quality result, the connection between the two devices should not exceed a certain distance (see audio/video characteristics table). For longer connections, it is necessary to provide a booster system in the installation. The connectors are type A and conform to the HDMI standard. Equipped with a 15 cm cord and 2 female connectors.

Range

Designation	Item
Pre-connected HDMI 2.0 connector	□ JW4284P
- 1 module	■ JG4284P
	■ JB4284P

Colors: □ White ■ Grey ■ Black

Overall dimensions (mm)



A	B	C	D	E	F
45.1	22.5	23	7.6	37	156

Connection

Values indicated for an installation set up in accordance with best practice and connected in compliance with existing standards. Any additional accessories and cords should comply with these same criteria.

FOR CONNECTION DIAGRAM SEE SHEET 2

Technical characteristics

- **Protection index:**
(considering a complete installation, including cover plate)
 - Penetration by solid bodies/liquid: IP20
 - Impact test: IK04
- **Material characteristics:**
 - Key cover: ABS
 - Halogen Free
 - UV resistant
 - Self-extinguishing: 650°C/30s
- **Climatic characteristics:**
 - Storage temperature: -10° C a +70° C
 - Use temperature: -5° C a +35° C

Cleaning

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals


Compliant with product and installation standard.

Refer to e.catalogue.

Pre-connected HDMI 2.0 connector

HDMI version 1.4

Max. resolution (pixels): 1080 p




HDMI version 2.0

Max resolution (pixels): 2160p

Format 16/9: 2160p, 60Hz, RGB

Format 21/9: 3840 x 2160p, 60Hz, RGB

Configuration 1



Configuration 2

