



On-Q
14-inch Enclosure, No Cover
Part No. EN1480



This 14" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

Features & Benefits

Includes five openings on the top of the enclosure with knockouts

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Made in the USA

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023050	Country Of Origin	United States
Application Sector	Residential	Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS
Type	Enclosure		

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Thickness	0.1 in	Frame	Cold Rolled Steel
-----------	--------	-------	-------------------