



On-Q
20-inch Enclosure with Screw-On Cover
Part No. EN2000



This 20" enclosure universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flex

Features & Benefits

20-in Enclosure with Screw-On Cover

Flush and surface installation

Patented mounting system offers versatile module mounting options

Includes self-adhesive cable identification table

Made in the USA

Drywall depth indicators

Mounting tabs provide correct flush-mount position for standard installations

Literature pouch included for dealer information

Cover included

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023067	Country Of Origin	United States
Application Sector	Residential	Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS
Type	Enclosure		

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	20.0 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Thickness	0.1 in	Cable Entry	(3) top knockouts
-----------	--------	-------------	-------------------

Frame	Cold Rolled Steel
-------	-------------------