



adorne Collection
adorne Paddle LED Advanced Dimmer, White
Part No. ADPD153LW2



Upgrade your space with the Legrand LED dimmer switch in the adorne® Collection. Designed specifically for flicker-free control of today's dimmable LED light bulbs and fixtures, this dimmer features advanced circuitry to offer a superior lighting control experience that works right out of the box. The dimmer switch boasts a variety of user adjustments to adapt to a wide range of dimmable LED lights, eliminating unpleasant flickering, pop-ons and more. As a part of the adorne® Collection, the advanced dimmer for LED lights also features clean lines and smooth control for a sophisticated touch. Pair with a screwless adorne® Wall Plate and other designer switches and outlets from the Collection for a cohesive design throughout the home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately. *Not intended for use with 0-10V, Magnetic Low Voltage and Electronic Low Voltage Drivers.

Features & Benefits

Specifically designed for use with dimmable LED bulbs and fixtures up to 150W at 120VAC. Optimized to work out of the box, and provide flicker-free control of LEDs. *Not intended for use with 0-10V, Magnetic Low Voltage, or Electronic Low Voltage Drivers

Advanced dimming technology maximizes LED compatibility to provide a full range of control while helping to eliminate most common LED dimming issues.

Replaces any basic single-pole or 3-way switch or dimmer in less than 15 minutes. No neutral wire required, works in both new construction and retrofit applications.

QR code provided on front face of device to provide easy access to installation guides and videos.

Optional LED Burst Mode setting can be activated as needed to help eliminate or reduce LED turn on delays and pop-ons.

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban antimicrobial technology

Simple high-and-low end dimming limit adjustability with easy-to-push calibration button to meet all lighting preferences and eliminate LED flickering.

Back-wire screw and pressure plate terminations for easy and reliable wiring with ground wire lead and wire nut provided.

Constant memory feature returns light levels and user adjustments to return to previous settings following a power failure or outage.

For complete installation, device must be paired with an adorne screwless Wall Plate (not included)

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007450705
Country Of Origin	China	Material	Polycarbonate

Features	Antimicrobial Protection, High-End Trim (Dim Range), LED Burst Mode, Low-End Trim (Dim Range)	Switch Type	Paddle, Slider
Number of Switches	1	Application Sector	Hospitality, Residential
Warranty Type	Limited Lifetime Warranty		
Dimensions			
Product Width US	1.77 in	Product Weight US	0.15 lb
Product Depth US	1.37 in	Product Height US	2.7 in
Product Length US	1.71 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
Energy Savings	Yes		
Technical Information			
Preset	Yes	Load Rating	120V 1.25A 150W (CFL), 120V 1.25A 150W (Incandescent), 120V 1.25A 150W (LED)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Poles	Single Pole 3-Way	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC

Load Type

LED
