



## adorne Collection

**Discontinued - adorne® sofTap™ Wi-Fi Ready Master Incandescent / Halogen Dimmer, Magnesium**  
Part No. ADTP600RMHM1



The sofTap Wi-Fi Ready Master Dimmer is a programmable light switch and dimmer combination that pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Manually turn lights on/off or adjust their brightness with the soft tap of a finger, or enjoy mobile control and create custom lighting scenes to control lights through the Legrand Lighting Control app for smartphones or tablets. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Pair with a sofTap Wi-Fi Ready Remote Dimmer for 3-way control. Simply follow the provided instructions after installing to pair with the Master Dimmer. For use with incandescent/halogen bulbs.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

|              |                                                 |                    |                                  |
|--------------|-------------------------------------------------|--------------------|----------------------------------|
| Product Line | Pass & Seymour                                  | Color              | Magnesium                        |
| UPC Number   | 804428065685                                    | Country Of Origin  | United States                    |
| Material     | Lexan, Polycarbonate                            | Features           | Indicator Lights, Smart Lighting |
| Switch Type  | sofTap                                          | Number of Switches | 1                                |
| Works With   | Amazon Alexa, Google Assistant, Radio Frequency | Application Sector | Residential                      |
| Standard     | cULus, FCC, UL 1472                             | Warranty Type      | 2-Year Limited Warranty          |

### Listing Agencies / 3rd Party Agencies

|              |     |               |     |
|--------------|-----|---------------|-----|
| cULus Listed | Yes | FCC Compliant | Yes |
|--------------|-----|---------------|-----|

---

Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

Technical Information

---

|                 |   |          |       |
|-----------------|---|----------|-------|
| Number of Gangs | 1 | Amperage | 5.5 A |
|-----------------|---|----------|-------|

---

|                    |                       |                 |                                    |
|--------------------|-----------------------|-----------------|------------------------------------|
| Bulb Compatibility | Halogen, Incandescent | Number of Poles | 3-Way, Multi-Location, Single Pole |
|--------------------|-----------------------|-----------------|------------------------------------|

---

|                       |     |         |       |
|-----------------------|-----|---------|-------|
| Requires Neutral Wire | Yes | Wattage | 600 W |
|-----------------------|-----|---------|-------|

---

|               |     |                 |                          |
|---------------|-----|-----------------|--------------------------|
| Mounting Type | Box | Connection Type | Internal Pressure Plates |
|---------------|-----|-----------------|--------------------------|

---

|                          |                                              |  |  |
|--------------------------|----------------------------------------------|--|--|
| Environmental Conditions | 0 to 80% (relative humidity, non-condensing) |  |  |
|--------------------------|----------------------------------------------|--|--|

---