



adorne Collection
adorne® 700W sofTap® Tru-Universal Dimmer, Magnesium, with Microban®
Part No. ADTP703TUM4



Turn lights on or off, or even dim them, with just a soft tap of a finger thanks to inventive micro-movement technology. Plus, as a Tru-Universal Dimmer, this dimmer switch self-calibrates to work with virtually any 120V dimmable bulb or fixture (excludes 0-10V). Always adjust to the precise light level you want, without the flicker.

This dimmer* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne Registered Collection at some partner locations may not yet include Microban Registered protection. To confirm that a specific Legrand product is protected with Microban Registered, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required.

Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Perfect for adding precise light level control – all it takes is a soft tap to turn on/off or adjust brightness.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Metallic	UPC Number	785007023176
Country Of Origin	China	Material	Polycarbonate

Features	Antimicrobial Protection, Auto-Calibration (Trim), High-End Trim (Dim Range), Locator Light, Low-End Trim (Dim Range)		Switch Type	Digital, sofTap
Number of Switches	1		Application Sector	Commercial, Hospitality, Residential
Warranty Type	Limited Lifetime Warranty		Type	Dimmer
Dimensions				
Product Width US	1.79 in		Product Depth US	1.77 in
Product Height US	4.2 in			
Technical Information				
Preset	Yes		Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 5.5A (EFL), 120V 500VA (MLV), 120V 700W (ELV), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward or Reverse Selectable Phase		Frequency Rating	60 Hz
Number of Poles	Single Pole 3-Way		Wire Size	#14 - #10 AWG
Requires Neutral Wire	Yes		Indoor/Outdoor	Indoor
Mounting Type	Wall Box		Wire Connection Type	Screw Terminals
Voltage	120 VAC		Load Type	CFL, Fluorescent, Halogen, Incandescent, LED