



adorne Collection
adorne® 3.1A Dual USB Outlet Module, Type A, Plus-Size, White
Part No. ARTRUSB153W4



Get a full battery for your phones, tablets and more with the convenience of built-in charging. Including two USB Type-A connections and replacing a traditional outlet in as little as ten minutes, this adorne USB Outlet provides easy-to-access charging without sacrificing a plug or finding that bulky adapter. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate(not included). Available in a range of contemporary colors and stunning finishes.

Features a total charging capacity of 3.1A.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisible shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Replaces a traditional outlet easily, in as little as 10 minutes.

Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007109931
Country Of Origin	China	Number of Receptacles	2
Features	USB-A Charging	Outlet Type	Tamper-Resistant, USB-Charging
Application Sector	Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL Listed	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.77 in	Product Depth US	1.48 in
Product Height US	2.65 in		

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back Only
USB Wattage	15 W	USB Amperage	3.1 A
Phase	Single	Number of USBs	2
Number of Wires	3	Number of Gangs	1
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
Mounting Type	Box	Wire Connection Type	Internal Pressure Plates
Voltage	125.0 V	Environmental Conditions	95% (relative humidity, non-condensing)