



adorne Collection
adorne® Motion Sensor Switch, Auto On/Off, Graphite, with Microban®
Part No. ASOS32G4



Perfect for pantries, garages or anywhere you want lights to turn on automatically when you enter a room, and turn off again when you leave. The Auto-On/Auto-Off SensaSwitch Registered provides convenient lighting control by responding to your presence through motion-sensing technology. Use this motion sensor light switch on its own to control a light or fixture from a single location, or pair with additional switches to control a single light source from multiple locations (3 or 4-way applications).

This switch* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne Registered Collection at some partner locations may not yet include Microban Registered protection. To confirm that a specific Legrand product is protected with Microban Registered, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in single-pole or 3-way applications. Must be paired with another SensaSwitch or SensaDimmer for 3-way control.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Features motion-sensing technology for automatic on/off lighting control. (Auto shut-off can be set from 5 to 30 minutes after vacancy.)

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Graphite
Finish	Metallic	UPC Number	785007234794
Country Of Origin	China	Material	Polycarbonate

Features	Adjustable Time Delay, Antimicrobial Protection, Light Level Sensor, Motion Sensor	Switch Type	Motion Sensor, sofTap
Number of Switches	1	Installation Location	Wall Box
Application Sector	Hospitality, Light Commercial, Multi-Dwelling Unit, Residential	Warranty Type	Limited Lifetime Warranty
Dimensions			
Product Width US	1.85 in	Product Depth US	1.77 in
Product Height US	2.66 in		
Technical Information			
Load Rating	120V 5A (ELV), 120V 5A 600W (CFL), 120V 5A 600W (LED), 120V 600VA (Fluorescent), 120V 600VA (MLV), 120V 600W (Halogen), 120V 600W (Incandescent)	Horsepower Rating	1/6 HP @ 120 VAC
Sensor Coverage Pattern	180 °	Sensor Type	Occupancy, Vacancy
Sensor Technology	Passive Infrared (PIR)	Timer Duration	15 Minutes, 30 Seconds-30 Minutes
Number of Poles	Single Pole 3 Way	Wire Size	#14 - #12 AWG
Input Voltage	120 VAC	Requires Neutral Wire	No
Line Frequency	60 Hz	Indoor/Outdoor	Indoor
Sensor Coverage	600 sq ft	Mounting Type	Wall Box
On Function	Selectable Auto/Manual	Operating Humidity	0-95% RH (Non-Condensing)
Sensing Range	Major Motion 35 ft, Minor Motion 20 ft	Location Rating	Dry
Wire Connection Type	Screw Terminals	Connection Type	Internal Pressure Plates
Load Type	CFL, Fan Motor, Fluorescent, Halogen, Incandescent, LED		