



adorne Collection
Discontinued - adorne® Touch Wi-Fi Ready Remote Switch, Magnesium
Part No. ASTHRRW1



Working in conjunction with an adorne Hub and a Touch Wi-Fi Ready Master Switch for 3-way control. Use the switch to turn lights on/off with a simple touch. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes. Installs in 25 minutes or less.

Allows 3-way application when paired with a Wi-Fi Ready Master Switch, letting you control a light or fixture from an additional location without running new wires. Pair with the Wi-Fi Ready Master Switch via the easy-to-follow instructions. Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems. Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	804428065845	Country Of Origin	China
Material	Lexan, Polycarbonate	Features	Smart Lighting
Switch Type	Touch	Number of Switches	1
Works With	Amazon Alexa, Control4, Elan, Google Assistant, Radio Frequency, RTI, URC	Application Sector	Residential
Standard	UL 508, FCC cULus, RoHS	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.77 in	Product Depth US	1.63 in
Product Height US	2.66 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Number of Gangs	1	Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon
Number of Poles	3-Way, Multi-Location, Single Pole	Requires Neutral Wire	Yes
Wattage	600 W	Mounting Type	Box
Supply Voltage	120 V	Location Rating	Dry
Connection Type	Internal Pressure Plates	Environmental Conditions	0 to 80% (relative humidity, non-condensing)