



adorne Collection
adorne® Motion Sensor Switch, Manual On/Auto Off, Magnesium, with Microban®
Part No. ASVS12M4



From bedrooms to basements, this motion sensor switch is perfect for anywhere you might want to worry (or waste electricity) less. A conveniently modern light switch, it features combination control that allows you to manually turn lights on when entering a room, and then automatically turns the lights off for you when you leave. Use this device on its own to control a light or fixture from a single location one location, or combine with additional switches for controlling a single light source from multiple locations in 3 or 4-way applications.

This switch* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne Registered Collection at some partner locations may not yet include Microban Registered protection. To confirm that a specific Legrand product is protected with Microban Registered, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Uses SensaSwitch technology to automatically turn lights off after you leave. (Auto shut-off can be set from 5 to 30 minutes after vacancy.)

Usable in single-pole or 3-way applications. Must be paired with another SensaSwitch or SensaDimmer for 3-way control.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Metallic	UPC Number	785007023282
Country Of Origin	China	Material	Polycarbonate
Features	Adjustable Time Delay, Antimicrobial Protection, Light Level Sensor, Motion Sensor	Switch Type	Motion Sensor, sofTap
Number of Switches	1	Installation Location	Wall Box

Application Sector	Hospitality, Light Commercial, Multi-Dwelling Unit, Residential	Standard	cULus
Warranty Type	Limited Lifetime Warranty		
Dimensions			
Product Width US	1.77 in	Product Depth US	1.85 in
Product Height US	2.66 in		
Technical Information			
Load Rating	120V 5A (ELV), 120V 5A 600W (CFL), 120V 5A 600W (LED), 120V 600VA (Fluorescent), 120V 600VA (MLV), 120V 600W (Halogen), 120V 600W (Incandescent)	Connector	Screw Terminals
Horsepower Rating	1/6 HP @ 120 VAC	Sensor Coverage Pattern	180 °
Sensor Type	Vacancy	Sensor Technology	Passive Infrared (PIR)
Timer Duration	15 Minutes, 30 Seconds-30 Minutes	Number of Poles	3 Way, Single Pole
Wire Size	#14 - #10 AWG	Input Voltage	120 VAC
Requires Neutral Wire	No	Line Frequency	60 Hz
Indoor/Outdoor	Indoor	Sensor Coverage	600 sq ft
Mounting Type	Wall Box	On Function	Manual On
Operating Humidity	0-95% RH (Non-Condensing)	Sensing Range	Major Motion 35 ft, Minor Motion 20 ft
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Connection Type	Internal Pressure Plates	Sensitivity	Major Motion 35', Minor Motion 20'
Load Type	CFL, Fan Motor, Fluorescent, Halogen, Incandescent, LED	Environmental Conditions	Residential Indoor Use Only