



adorne Collection  
**adorne® Mirror Black 1-Gang+ Screwless Wall Plate**  
Part No. AWM1G3MB4



Modern and dramatic, add a luxurious feel to any room with this dark reflective finish. A 2-Gang Wall Plate, it is perfectly sized to fit any combination of up to two standard-sized adorne devices, or up to four half-sized adorne designer switches and outlets.

## Features & Benefits

- Includes one Wall Plate and one Steel Frame for mounting the wall plate.
- Made to exclusively fit the designer switches, dimmers and outlets from the adorne® Collection, snapping into place with ease.
- Coordinate with other designer switches and outlets throughout your home for a cohesive, contemporary look.
- A perfect finishing touch for any space, adding a sleek and contemporary aesthetic through its screwless design and low-profile.
- Other Wall Plates from the adorne® Collection are available in extensive range of on-trend colors, materials and cast metals.

## Specifications

### General Info

|                   |                                   |                    |                           |
|-------------------|-----------------------------------|--------------------|---------------------------|
| Product Line      | Pass & Seymour                    | Color              | Mirror Black              |
| Finish            | Gloss                             | UPC Number         | 785007024500              |
| Country Of Origin | Mexico                            | Material           | Non-Metallic              |
| Construction      | Screwless Design Snaps into Frame | Wall Plate Size    | Plus                      |
| Wall Plate Type   | Dimmer/Switch, Outlet             | Application Sector | Commercial, Residential   |
| Standard          | cULus UL514, cETLus               | Warranty Type      | Limited Lifetime Warranty |
| Type              | Wall Plate                        |                    |                           |

## Dimensions

|                       |          |                  |           |
|-----------------------|----------|------------------|-----------|
| Product Width US      | 3.45 in  | Product Depth US | 0.35 in   |
| Product Height US     | 5.13 in  |                  |           |
| Technical Information |          |                  |           |
| Thickness             | 0.07 in  | Number of Gangs  | 1         |
| Indoor/Outdoor        | Indoor   | Mounting Type    | Screwless |
| Orientation           | Vertical |                  |           |