



adorne Collection
adorne® Titanium 2-Gang Screwless Wall Plate
Part No. AWP2GTM4



Subtle but lustrous, this finish is charismatic enough to fit in anywhere. Made exclusively for use with designer switches and outlets from the adorne Registered Collection. This wall plate* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product. * Existing inventory of switches, dimmers and plastic wall plates from the adorne Registered Collection at some partner locations may not yet include Microban Registered protection. To confirm that a specific Legrand product is protected with Microban Registered, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label. No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology.

Made to exclusively fit the designer switches, dimmers and outlets from the adorne® Collection, snapping into place with ease.

Coordinate with other designer switches and outlets throughout your home for a cohesive, contemporary look.

Includes one Wall Plate and one Steel Frame for mounting the wall plate.

Other Wall Plates from the adorne® Collection are available in extensive range of on-trend colors, materials and cast metals.

A perfect finishing touch for any space, adding a sleek and contemporary aesthetic through its screwless design and low-profile.

Specifications

General Info

Product Line	Pass & Seymour	Color	Titanium
Finish	Frosted	UPC Number	785007024760
Country Of Origin	Mexico	Material	Polycarbonate
Construction	Plastic	Wall Plate Type	Dimmer/Switch, Outlet
Application Sector	Commercial, Residential	Standard	cULus UL514, cETLus
Warranty Type	Limited Lifetime Warranty	Type	Wall Plate

Dimensions

Product Width US	5.29 in	Product Depth US	0.35 in
------------------	---------	------------------	---------

Product Height US	5.13 in
-------------------	---------

Technical Information

Thickness	0.07 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Screwless
Orientation	Vertical		