



Pass and Seymour
15A, 125V Watertight Straight Blade Plug, Yellow
Part No. 14W47



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Color-coded sealing bushings provided for a large range of cord diameters.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007114140	Country Of Origin	United States
Features	Watertight	Application Sector	Industrial
Standard	UL498	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	1.85 in	Product Depth US	2.62 in
------------------	---------	------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	146159
------------	-----	-----------------	--------

Technical Information

Connector Style	Straight Blade	Flanged	No
Terminal Accommodation	#14 AWG - #10 AWG	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Both	NEMA Configuration Code	5-15P
Voltage	125.0 V		