



Pass and Seymour
Tamper-Resistant Floor Box Assembly, One-Gang for Wood Sub-Floors, Brass Plate
Part No. 1542TRDR



Tamper-Resistant Display Receptacle, 15A 125V With Brass Plate and plug.

Features & Benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly
- Easily accessed break-off line contact connecting tab for fast and easy split circuit wiring
- .032 inch thick brass triple-wipe power contacts for lasting retention
- Auto-ground clip assures positive ground

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
Finish	Metallic	UPC Number	785007108767
Country Of Origin	Mexico	Material	Brass
Cover Type	Tamper-Resistant	Features	Recessed
Application Sector	Commercial	Wall Plate Included	No
Standard	cULus, Fedspec	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	2.75 in	Product Weight US	0.53 lb
------------------	---------	-------------------	---------

Product Depth US	1.825 in	Product Height US	4.5 in
Product Length US	4.5 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Connection Location	Side Only	Number of Wires	3
Number of Gangs	1	Number of Poles	3-Way
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Mounting Type	Screw Mount	Box Cover Position	Vertical
Wire Connection Type	Screw Terminals	Voltage	125.0 V
Environmental Conditions	85% (relative humidity, non-condensing)		