



Pass and Seymour
15A, 125V Rubber Dust-Tight Connector, Yellow
Part No. 1547



Straight Blade Rubber Connector 15amp 125volt 5-15r

Features & Benefits

Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.

Floating blades allow self-alignment with contacts for a firm, even electrical connection.

Terminal screws backed-out, ready-to-wire, saving time and money.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Quick-drive assembly screws allow for fast installation, saving time and money.

Self-centering cord clamps provide superior strain relief.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007114126	Country Of Origin	United States
Features	Dust Resistant	Application Sector	Industrial
Standard	UL498	Warranty Type	1-Year
Type	Connector		

Dimensions

Product Width US	1.53 in	Product Height US	2.99 in
------------------	---------	-------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	146159
Technical Information			
Connector Style	Straight Blade	Flanged	No
Terminal Accommodation	#14 AWG - #10 AWG	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Voltage	125.0 V		