



## radiant Collection

### radiant® Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with Audible Alarm and SafeLock® Protection, Light Almond

Part No. 1597TRALA



GFCI outlets from the radiant Registered Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code for ground fault protection in the home, GFCI outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. This model includes an optional audible alarm, so trips never go unnoticed, and is great for appliances where loss of power could cause damage, such as freezers and sump pumps. Maximize safety, in style, with GFCI protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

## Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

Audible Alarm alerts when a trip occurs. Alarm rated at 60 dB at 10 feet and can be turned ON/OFF.

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.

Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                    |                                              |                       |                                   |
|--------------------|----------------------------------------------|-----------------------|-----------------------------------|
| Product Line       | Pass & Seymour                               | Color                 | Light Almond                      |
| Finish             | Satin                                        | UPC Number            | 785007047974                      |
| Country Of Origin  | China                                        | Number of Receptacles | 2                                 |
| Features           | Audible Alarm, Self-Test                     | Outlet Type           | GFCI, Self-Test, Tamper-Resistant |
| Application Sector | Commercial, Multi-Dwelling Unit, Residential | Wall Plate Included   | Yes                               |
| Standard           | cULus, UL Listed, FSUL                       | Warranty Type         | 1-Year Limited Warranty           |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.73 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in  |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E42190 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

### Technical Information

|                     |     |                     |               |
|---------------------|-----|---------------------|---------------|
| Is Tamper-Resistant | Yes | Connection Location | Back and Side |
|---------------------|-----|---------------------|---------------|

|                 |         |                          |                                           |
|-----------------|---------|--------------------------|-------------------------------------------|
| Number of Wires | 3       | Number of Gangs          | 1                                         |
| Amperage        | 15 A    | Number of Poles          | Double Pole                               |
| Indoor/Outdoor  | Indoor  | NEMA Configuration Code  | 5-15R                                     |
| Mounting Type   | Box     | Wire Connection Type     | Internal Pressure Plates, Screw Terminals |
| Voltage         | 125.0 V | Environmental Conditions | 95% Humidity, UL 94 V2                    |