



Pass and Seymour
Discontinued - In Line Portable 20A GFCI, Manual Reset
Part No. 2094TL2M

Portable Ground Fault Circuit Interrupter, 20amp 125volt 2' Cord,
Manual Reset



Features & Benefits

In-line portable GFCI interrupter

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	2097TL2M
UPC Number	785007263954	Country Of Origin	China
Application Sector	Commercial, Residential	Standard	cULus, UL943, UL498, C22.2 No. 144, C22.2 No. 42, ROHS-Compliant

Dimensions

Product Width US	3.5 in	Product Weight US	56.0 lb
Product Height US	2.0 in	Product Length US	8.0 in

Technical Information

Operating Temperature Min	-30 °F	Phase	Single
Connection	Side and back wire.	Operating Temperature Max	150 °F
Amperage	20 A	Number of Poles	Double Pole

Operating Temperature	-30°-150°F, -35°-66°C	Environmental Conditions	-35C(-30F) to +66C(150F)
-----------------------	-----------------------	--------------------------	--------------------------
