



Pass and Seymour
Hospital Grade 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Gray
Part No. 2097HGGRY



Hospital-Grade 20A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade GFCI self-test

One-piece, brass, triple-wipe power contacts for lasting retention.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007035711
Country Of Origin	China	Number of Receptacles	2
Features	Self-Test	Outlet Type	GFCI, Hospital Grade
Application Sector	Commercial, Healthcare	Wall Plate Included	Yes
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connection Location	Back and Side	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	125.0 V