



Hospital-Grade Tamper-Resistant Weather-Resistant 15A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade GFCI self-test CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle.

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007180664	Country Of Origin	China
Number of Receptacles	2	Features	Self-Test, Weatherproof
Outlet Type	GFCI, Hospital Grade, Tamper-Resistant, Weather-Resistant	Application Sector	Commercial, Healthcare
Wall Plate Included	Yes	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.73 in	Product Depth US	1.13 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Both
NEMA Configuration Code	5-20R	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	125.0 V		