



Hospital-Grade Isolated Ground Tamper-Resistant 20A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade GFCI self-test

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007047882	Country Of Origin	China
Number of Receptacles	2	Features	Isolated Ground, Self-Test
Outlet Type	GFCI, Hospital Grade, Tamper-Resistant	Application Sector	Commercial, Multi-Dwelling Unit, Residential
Wall Plate Included	Yes	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	125.0 V	Environmental Conditions	95% Humidity, UL 94 V2