



Single-Pole, Back and Side-Wire, Decorator Switch, 15A, 120/277V

Features & Benefits

Impact-resistant polycarb back body and frame.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Integral auto-ground clip for positive ground to metal boxes.

Tri-drive ground, terminal, and mounting screws.

All terminal screws backed out, ready-to-install.

For covering patents, see

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007539035
Country Of Origin	Mexico	Material	Thermoplastic
Features	Decorator Style	Switch Type	Paddle
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 20
Warranty Type	1-Year Limited Warranty	Type	Decorator, Switch

Dimensions

Product Width US	1.3 in	Product Depth US	1.03 in
------------------	--------	------------------	---------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140597
------------	-----	---------------------	--------

cULus Listed	Yes	CSA File Number	17446
--------------	-----	-----------------	-------

Technical Information

Operating Temperature Min	-4 °F	Load Rating	15 A @ 120/277 VAC
---------------------------	-------	-------------	--------------------

Connection Location	Back and Side	Horsepower Rating	1/2 HP @ 120 VAC, 2 HP @ 240 VAC
---------------------	---------------	-------------------	----------------------------------

Terminal Accommodation	#14 AWG - #10 AWG	Operating Temperature Max	140 °F
------------------------	-------------------	---------------------------	--------

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Single Pole	Requires Neutral Wire	No
-----------------	-------------	-----------------------	----

Indoor/Outdoor	Indoor	Mounting Type	Wall Box
----------------	--------	---------------	----------

Operating Temperature	-20°-60°C, -4°-140°F	Wire Connection Type	Screw Terminals
-----------------------	----------------------	----------------------	-----------------

Voltage	120 VAC, 277 VAC	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon
---------	------------------	-----------	--
