



Single-Pole, Back and Side-Wire, Decorator Switch, 20A, 120/277V.

Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007539301
Country Of Origin	Mexico	Material	Thermoplastic
Features	Decorator Style	Switch Type	Paddle
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 20

Warranty Type	1-Year Limited Warranty	Type	Decorator, Switch
Dimensions			
Product Width US	1.3 in	Product Depth US	1.06 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus ListingNumber	140597
cULus Listed	Yes	CSA File Number	17446
Technical Information			
Operating Temperature Min	-4 °F	Load Rating	20 A @ 120/277 VAC
Connection Location	Back and Side	Terminal Accommodation	#14 AWG - #10 AWG
Operating Temperature Max	140 °F	Number of Gangs	1
Throw Type	Single Throw	Amperage	20 A
Number of Poles	Single Pole	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Operating Temperature	-20°-60°C, -4°-140°F	Wire Connection Type	Screw Terminals
Voltage	120/277 V	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon