



Pass and Seymour  
20A 120V/277V Specification Grade Single Pole Decorator Paddle Switch, Red  
Part No. 2621RED

Single-Pole, Back and Side-Wire, Decorator Switch, 20A, 120/277V.



## Features & Benefits

|                                                                                                                          |                                                                                                                                             |
|--------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|
| Impact-resistant polycarb back body and frame.                                                                           | Cushioned thermoplastic paddle assures smooth, quiet, long term operation.                                                                  |
| Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts. | Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire. |
| Terminals made of high conductivity brass and serrated for maximum wire gripping.                                        | Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.                                             |
| Integral auto-ground clip for positive ground to metal boxes.                                                            | Tri-drive ground, terminal, and mounting screws.                                                                                            |
| All terminal screws backed out, ready-to-install.                                                                        | For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .                                              |

## Specifications

### General Info

|                     |                 |                    |                        |
|---------------------|-----------------|--------------------|------------------------|
| Product Line        | Pass & Seymour  | Color              | Red                    |
| Finish              | Matte           | UPC Number         | 785007539349           |
| Country Of Origin   | Mexico          | Material           | Thermoplastic          |
| Features            | Decorator Style | Switch Type        | Paddle                 |
| Number of Switches  | 1               | Application Sector | Commercial, Industrial |
| Wall Plate Included | No              | Standard           | UL 20                  |

|                                       |                         |                        |                                                                |
|---------------------------------------|-------------------------|------------------------|----------------------------------------------------------------|
| Warranty Type                         | 1-Year Limited Warranty | Type                   | Decorator, Switch                                              |
| Dimensions                            |                         |                        |                                                                |
| Product Width US                      | 1.3 in                  | Product Depth US       | 1.06 in                                                        |
| Product Height US                     | 4.2 in                  |                        |                                                                |
| Listing Agencies / 3rd Party Agencies |                         |                        |                                                                |
| CSA Listed                            | Yes                     | cULus ListingNumber    | 140597                                                         |
| cULus Listed                          | Yes                     | CSA File Number        | 17446                                                          |
| Technical Information                 |                         |                        |                                                                |
| Operating Temperature Min             | -4 °F                   | Load Rating            | 20 A @ 120/277 VAC                                             |
| Connection Location                   | Back and Side           | Terminal Accommodation | #14 AWG - #10 AWG                                              |
| Operating Temperature Max             | 140 °F                  | Number of Gangs        | 1                                                              |
| Throw Type                            | Single Throw            | Amperage               | 20 A                                                           |
| Number of Poles                       | Single Pole             | Requires Neutral Wire  | No                                                             |
| Indoor/Outdoor                        | Indoor                  | Mounting Type          | Wall Box                                                       |
| Operating Temperature                 | -20°-60°C, -4°-140°F    | Wire Connection Type   | Screw Terminals                                                |
| Voltage                               | 120/277 V               | Load Type              | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |