



Pass and Seymour  
20A 125V Heavy Duty Spec-Grade Decorator Duplex Receptacle, Back and Side Wire, Red  
Part No. 26342RED



Heavy-Duty Decorator Spec Grade Duplex Receptacle Side Wire 20A 125V

## Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. Rated 15 amperes

Heavy-duty compact design for easier installation and long lasting performance.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face.

Terminal compartments isolated from each other for positive conductor containment.

Tri-drive terminal and mounting screws.

Auto-ground clip assures positive ground

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                       |                         |                    |                                                           |
|-----------------------|-------------------------|--------------------|-----------------------------------------------------------|
| Product Line          | Pass & Seymour          | Color              | Red                                                       |
| UPC Number            | 785007785234            | Country Of Origin  | Mexico                                                    |
| Number of Receptacles | 2                       | Features           | Decorator Style, Single Piece Plated Steel Mounting Strap |
| Outlet Type           | Straight Blade          | Application Sector | Commercial                                                |
| Wall Plate Included   | No                      | Standard           | UL498, cUL CSA, FEDSPEC                                   |
| Warranty Type         | 1-Year Limited Warranty |                    |                                                           |

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.322 in | Product Depth US | 0.833 in |
| Product Height US | 2.635 in |                  |          |

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

|                          |                          |                         |             |
|--------------------------|--------------------------|-------------------------|-------------|
| Dielectric Strength      | Withstands 2000V minimum | Connection Location     | Side Only   |
| Number of Wires          | 3                        | Amperage                | 20 A        |
| Number of Poles          | Double Pole              | Wire Size               | 14 - 10 AWG |
| Indoor/Outdoor           | Indoor                   | NEMA Configuration Code | 5-20R       |
| Wire Connection Type     | Screw Terminals          | Voltage                 | 125.0 V     |
| Environmental Conditions | Flammability: UL94 V2    |                         |             |