



Pass and Seymour
20A 125V Heavy Duty Specification Grade Decorator Duplex Receptacle, Red
Part No. 26352RED



Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side Wire
20A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.	Heavy-duty compact design for easier installation and long lasting performance.
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.	Impact-resistant nylon face.
Terminal compartments isolated from each other for positive conductor containment.	All devices fit standard #26 opening wall plate.
Tri-drive terminal and mounting screws.	Auto-ground clip assures positive ground.
Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Finish	Matte	UPC Number	785007785395
Country Of Origin	Mexico	Number of Receptacles	2
Features	Decorator Style, Single Piece Plated Steel Mounting Strap	Outlet Type	Straight Blade
Application Sector	Commercial	Wall Plate Included	No

Standard	UL498, cUL CSA, FEDSPEC	Warranty Type	1-Year Limited Warranty
Dimensions			
Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection Location	Back and Side
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	125.0 V