



Pass and Seymour  
**20A 125V Heavy Duty Hospital-Grade Decorator Duplex Receptacle, Red**  
Part No. 26362HGREd

Heavy-Duty Decorator Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V



## Features & Benefits

|                                                                                                                                                                                                                               |                                                                                 |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------|
| Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.                                                                                                                   | Heavy-duty compact design for easier installation and long lasting performance. |
| Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.                                                                                                                                   | Impact-resistant nylon face.                                                    |
| Terminal compartments isolated from each other for positive conductor containment.                                                                                                                                            | All devices fit standard #26 opening wall plate.                                |
| Tri-drive terminal and mounting screws.                                                                                                                                                                                       | Auto-ground clip assures positive ground.                                       |
| Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |                                                                                 |

## Specifications

### General Info

|                    |                                                           |                       |                |
|--------------------|-----------------------------------------------------------|-----------------------|----------------|
| Product Line       | Pass & Seymour                                            | Color                 | Red            |
| Finish             | Matte                                                     | UPC Number            | 785007785586   |
| Country Of Origin  | Mexico                                                    | Number of Receptacles | 2              |
| Features           | Decorator Style, Single Piece Plated Steel Mounting Strap | Outlet Type           | Hospital Grade |
| Application Sector | Commercial, Healthcare                                    | Wall Plate Included   | No             |

|                                       |                         |                         |                          |
|---------------------------------------|-------------------------|-------------------------|--------------------------|
| Standard                              | UL498, cUL CSA, FEDSPEC | Warranty Type           | 1-Year Limited Warranty  |
| Dimensions                            |                         |                         |                          |
| Product Width US                      | 1.322 in                | Product Depth US        | 0.833 in                 |
| Product Height US                     | 2.635 in                |                         |                          |
| Listing Agencies / 3rd Party Agencies |                         |                         |                          |
| cULus ListingNumber                   | E140596                 | cULus Listed            | Yes                      |
| Technical Information                 |                         |                         |                          |
| Operating Temperature Min             | -40 °C                  | Dielectric Strength     | Withstands 2000V minimum |
| Connection Location                   | Back and Side           | Number of Wires         | 3                        |
| Operating Temperature Max             | 60 °C                   | Amperage                | 20 A                     |
| Number of Poles                       | Double Pole             | Wire Size               | 14 - 10 AWG              |
| Indoor/Outdoor                        | Indoor                  | NEMA Configuration Code | 5-20R                    |
| Operating Temperature                 | -40°-60°C               | Wire Connection Type    | Screw Terminals          |
| Voltage                               | 125.0 V                 |                         |                          |