



Pass and Seymour
Turnlok® Watertight Locking Plug, 20A 125V, NEMA 4X/6P Rated, NEMA L5-20P Config, Yellow
Part No. 26W47



Locking Watertight Plug, 20amp 125volt, NEMA Configuration L5-20, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P and IP67 rated.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather. Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Devices resist high-pressure hose down of 1,500 psi.

Color coded sealing bushings provided for large range of cord diameters

Large ribs on body for a superior grip when mating.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007032611	Country Of Origin	United States
Features	Watertight	Application Sector	Industrial
Standard	UL Listed, CSA Listed	Warranty Type	1-Year
Type	Locking, Plug		

Dimensions

Product Height US	1.85 in	Product Length US	2.62 in
-------------------	---------	-------------------	---------

Technical Information

Operating Temperature Min	-40 °C	Connector Style	Locking
Flanged	No	Terminal Accommodation	#14 AWG - #10 AWG
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	20 A	IP Rating	IP67
Number of Poles	Double Pole	Indoor/Outdoor	Both
NEMA Configuration Code	L5-20P	Operating Temperature	-40°-60°C
Number of Phases	1	Voltage	125.0 V

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
