



Pass and Seymour
Turnlok® 20A Watertight Connector, NEMA 4X/6P, Yellow
Part No. 27W47



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour Turnlok watertight plugs and connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color-coded sealing bushings provided for large range of cord diameters

For Covering Patents, see www.legrand.us/patents.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Devices resist high-pressure hosedown of 1,500 psi.

Large ribs on body for a superior grip when mating.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007032598	Country Of Origin	United States
Features	Watertight	Application Sector	Industrial
Standard	UL Listed, CSA Listed	Warranty Type	1-Year
Type	Connector		

Dimensions

Product Width US	1.85 in	Product Depth US	4.03 in
------------------	---------	------------------	---------

Product Height US	1.85 in		
Technical Information			
Operating Temperature Min	-40 °C	Connector Style	Locking
Flanged	No	Terminal Accommodation	#14 AWG - #10 AWG
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	20 A	IP Rating	IP67
Number of Poles	Double Pole	Indoor/Outdoor	Both
NEMA Configuration Code	L5-20R	Operating Temperature	-40°- 60°C
Number of Phases	1	Voltage	125.0 V
Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized		