



Locking Dust-Tight Rubber Connector, 30amp 125/250volt, NEMA Configuration L14-30.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather

Quick lead assembly screws aid in a fast installation

Keyed body and cover for easy assembly and alignment

Two Screw cable clamp secures wire and provides superior strain relief

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033748	Country Of Origin	United States
Features	Dust Resistant	Application Sector	Industrial
Standard	UL Listed, CSA Listed	Warranty Type	1-Year
Type	Connector		

Dimensions

Product Width US	2.3 in	Product Length US	4.04 in
------------------	--------	-------------------	---------

Technical Information

Operating Temperature Min	-40 °C	Connector Style	Locking
---------------------------	--------	-----------------	---------

Flanged	No	Terminal Accommodation	#12 AWG - #6 AWG
Number of Wires	4	Operating Temperature Max	75 °C
Amperage	30 A	Number of Poles	3-Way
Indoor/Outdoor	Indoor	NEMA Configuration Code	L14-30R
Operating Temperature	-40°-75°C	Number of Phases	1
Voltage	125/250 V	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature - 40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized