



Pass and Seymour
30A Non-NEMA 3 Wire Connector - Black Back, White Front Body
Part No. 3333SS

Control 30A 125/250V Turnlok Registered



Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Double dovetail design provides superior protection against cord pull-out forces.

Impact- and corrosion-resistant durable nylon 6 shell material.

Rounded back contour reduces snags and hang-ups on the job site.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible assurance of safe and proper cord retention.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007333312	Country Of Origin	Mexico
Features	Corrosion Resistant	Application Sector	Industrial
Standard	UL498, CSA C22.2 No. 42	Warranty Type	1-Year
Type	Connector		

Dimensions

Product Width US	2.56 in	Product Depth US	1.72 in
------------------	---------	------------------	---------

Product Height US	2.56 in
-------------------	---------

Technical Information

Connector Style	Locking	Flanged	No
Number of Wires	3	Amperage	30 A
Indoor/Outdoor	Indoor	Voltage	125/250 V
Environmental Conditions	Consult the Factory		