



Receptacle Single 30A 120/208V 3-Phase-y

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007343007
Country Of Origin	Mexico	Number of Receptacles	1
Features	Brass Mounting Strap, Impact Resistant	Outlet Type	Locking
Application Sector	Industrial	Wall Plate Included	No
Standard	UL498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.437 in	Product Depth US	1.2 in
Product Height US	2.25 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection Location	Back and Side	Phase	Three
---------------------	---------------	-------	-------

Number of Wires	4	Amperage	30 A
-----------------	---	----------	------

Number of Poles	3-Way	Wire Size	14 - 10 AWG
-----------------	-------	-----------	-------------

Indoor/Outdoor	Indoor	Wire Connection Type	Screw Terminals
----------------	--------	----------------------	-----------------

Voltage	120/208 V	Environmental Conditions	Consult the Factory
---------	-----------	--------------------------	---------------------