



Heavy Cast Aluminum Cover Mounting Plate for Decorator/Ground Fault Circuit Interruptor,

Features & Benefits

Adapter, frame, and cover are heavy cast aluminum.

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).

Neoprene gasket seals cover to frame. Moisture and dust cannot enter enclosure.

Purchase enclosure and mounting plate separately.

No. 8-32 screws hold assembly firmly in place.

Mortar keys provide positive holding means within wall.

Two keys provided for lock.

Mounts on 4 in. or 4-11/16 in. box.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Satin	UPC Number	785007179200
Country Of Origin	United States	Material	Aluminum, Cast Metals
Cover Type	Mortared-In Applications	Features	Dust Resistant, Moisture Resistant
Application Sector	Commercial, Industrial	Standard	UL Listed
Type	Weatherproof Cast Cover		

Dimensions

Product Width US	3.063 in	Product Weight US	0.06 lb
Product Depth US	0.78 in	Product Height US	3.094 in
Product Length US	3.094 in		

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Mounting Type	Box Mounted	Box Cover Position	Vertical
Number of Outlets	1		