



Heavy Cast Aluminum Cover Mounting Plate for Single Receptacle Diameter 2.156-in,



Features & Benefits

Adapter, frame, and cover are heavy cast aluminum.

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).

Neoprene gasket seals cover to frame. Moisture and dust cannot enter enclosure.

Purchase enclosure and mounting plate separately.

No. 8-32 screws hold assembly firmly in place.

Mortar keys provide positive holding means within wall.

Two keys provided for lock.

Mounts on 4 in. or 4-11/16 in. box.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Satin	UPC Number	785007179217
Country Of Origin	United States	Material	Aluminum, Cast Metals
Cover Type	Mortared-In Applications	Features	Dust Resistant, Moisture Resistant
Application Sector	Commercial, Industrial	Standard	UL/CSA Listed
Type	Weatherproof Cast Cover		

Dimensions

Product Width US	3.063 in	Product Depth US	0.78 in
Product Height US	3.094 in	Product Length US	3.094 in

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Box Cover Position	Vertical

Number of Outlets	1
-------------------	---
