

Turnlok Registered Duplex Receptacle 3-Wire 15A 125A



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007470000
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498		

Dimensions

Product Width US	1.5 in	Product Depth US	1.199 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
------------	-----	---------------------	--------

cULus Listed	Yes	CSA File Number	16063
--------------	-----	-----------------	-------

Technical Information

Phase	Three	Amperage	15 A
-------	-------	----------	------

Number of Poles	Double Pole		
-----------------	-------------	--	--