

Receptacle Duplex Combination



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007479201	Country Of Origin	United States
Number of Receptacles	2	Features	Brass Mounting Strap, Impact Resistant
Outlet Type	Locking, Straight Blade	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.5 in	Product Depth US	1.199 in
Product Height US	3.28 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	CSA File Number	135325
Technical Information			
Connection Location	Back and Side	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R, L5-15R	Wire Connection Type	Screw Terminals
Voltage	125.0 V		