



CC Commercial Grade Plug 15A Yellow

Features & Benefits

All nylon construction.

Termination saddle clamps securely capture stranded wires.

All yellow, perfect for high-visibility cords.

External cord grips are one-size-fits-all, no inserts or flipping the clamps to fit the proper cord OD.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007046038	Country Of Origin	China
Features	Durable	Application Sector	Industrial
Standard	UL498	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	1.563 in	Product Length US	1.688 in
------------------	----------	-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Connector Style	Straight Blade	Flanged	No
Terminal Accommodation	#14 AWG - #10 AWG	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15P
Voltage	125.0 V		