



Hard Use Spec Grade Duplex Receptacle Back and Side Wire 15A 125V



Features & Benefits

- Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
- LED Indication: Steady green = protected, Flashing re = not protected, OFF = no power to unit

Impact-resistant nylon face.

Terminal compartments isolated from each other for positive conductor containment.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

|                       |                |                    |                                          |
|-----------------------|----------------|--------------------|------------------------------------------|
| Product Line          | Pass & Seymour | Color              | Brown                                    |
| UPC Number            | 785007526202   | Country Of Origin  | Mexico                                   |
| Number of Receptacles | 2              | Features           | Single Piece Plated Steel Mounting Strap |
| Outlet Type           | Straight Blade | Application Sector | Commercial                               |
| Wall Plate Included   | No             | Standard           | UL498, CSA C22.2 No. 42, FDSPEC          |

|                                       |                          |                         |               |
|---------------------------------------|--------------------------|-------------------------|---------------|
| Warranty Type                         | 1-Year Limited Warranty  |                         |               |
| Dimensions                            |                          |                         |               |
| Product Width US                      | 1.322 in                 | Product Depth US        | 0.78 in       |
| Product Height US                     | 2.635 in                 |                         |               |
| Listing Agencies / 3rd Party Agencies |                          |                         |               |
| cULus ListingNumber                   | E140596                  | cULus Listed            | Yes           |
| Technical Information                 |                          |                         |               |
| Dielectric Strength                   | Withstands 2000V minimum | Connection Location     | Back and Side |
| Number of Wires                       | 3                        | Amperage                | 15 A          |
| Number of Poles                       | Double Pole              | Wire Size               | 14 - 10 AWG   |
| Indoor/Outdoor                        | Indoor                   | NEMA Configuration Code | 5-15R         |
| Wire Connection Type                  | Screw Terminals          | Voltage                 | 125.0 V       |
| Environmental Conditions              | Flammability: UL94 V2    |                         |               |