

Heavy-Duty Spec Grade Single Receptacle Side Wire 20A 125V



Features & Benefits

Auto-ground clip assures positive ground.

Factory-broken split-circuit tab allows for 50% plug load control to be achieved in one duplex receptacle.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate side wire capability.

One-piece brass triple-wire power contacts for lasting retention.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007535112
Country Of Origin	Mexico	Number of Receptacles	1
Features	Heavy Duty Steel Mounting Strap	Outlet Type	Straight Blade
Application Sector	Commercial	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.38 in	Product Depth US	1.08 in
------------------	---------	------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Connection Location	Side Only
---------------------------	--------	---------------------	-----------

Number of Wires	3	Operating Temperature Max	60 °C
-----------------	---	---------------------------	-------

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

NEMA Configuration Code	5-20R	Operating Temperature	-40°-60°C
-------------------------	-------	-----------------------	-----------

Voltage	125.0 V		
---------	---------	--	--