



Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.

LED Indication: Steady green = protected, Flashing red = not protected, OFF = no power to unit

Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.

Impact-resistant thermoplastic exterior resists impacts and scrapes.

Triple-wipe, copper-alloy contacts for superior, more dependable connection.

External screw-pressure-plate back and side wire terminals including ground with external back wire clamps (exclusive) accept #14 - #10 AWG copper or copper-clad, solid or stranded conductors.

External pressure plate feature allows two conductors to be terminated by a single screw.

Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection.

Protection response time in less than one nanosecond.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	5362BLSP
Color	Blue	UPC Number	785007193961
Country Of Origin	Mexico		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	20 A
----------	------