



Pass and Seymour
Discontinued - Heavy Duty Spec Grade Single Receptacles, Back and Side Wire, 15A, 250V, Light Almond
Part No. 5671LA



Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 250V

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

One-piece brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007548280
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	UL 498, WC596, FEDSPEC		

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cULus ListingNumber	E140596
cULus Listed	Yes	cUL Listed	Yes

Technical Information

Phase	Three	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG		