



Pass and Seymour
20A, 125V Watertight Single Receptacle, Yellow
Part No. 60W33



Straight Blade Watertight Single Receptacle, 20amp 125volt, NEMA Configuration 5-20, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033458	Country Of Origin	United States
Features	Watertight	Application Sector	Commercial
Standard	CSA Listed, FSUL, UL Listed	Warranty Type	1-Year
Type	Receptacle		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Operating Temperature Min	-40 °C	Connector Style	Straight Blade
Flanged	No	Terminal Accommodation	#18 AWG - #12 AWG

Connection	Cable	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Both
Operating Temperature	-40°-60°C	Number of Phases	1
Voltage	125.0 V	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized