



Pass and Seymour
15A, 125V Watertight Straight Blade, Single Receptacle, Yellow
Part No. 60W47



Pass and Seymour Watertight Receptacles and Back Boxes mining, mills and many other locations.

Features & Benefits

Impact-resistant Valox lid, cover plate and receptacle body withstand impacts, chemical & corrosion.

Stainless-steel hinge spring and pin ensure corrosion resistance.

Spring-loaded flip cover provides protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033694	Country Of Origin	United States
Application Sector	Commercial	Standard	CSA Listed, FSUL, UL Listed

Dimensions

Product Width US	3.0 in	Product Weight US	0.8 lb
Product Volume US	45.703 cu in	Product Depth US	3.125 in
Product Height US	4.875 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Operating Temperature Min	-40 °C	Phase	Single
Connection	Cable	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG
Operating Temperature	-40°-60°C	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized