



Pass and Seymour
15A, 250V Watertight Duplex Receptacle, Yellow
Part No. 60W49DPLX



Straight Blade Watertight Duplex Receptacle, 15amp 250volt, NEMA Configuration 6-15, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033151	Country Of Origin	United States
Application Sector	Commercial	Standard	CSA Listed, FSUL, UL Listed

Dimensions

Product Width US	1.85 in	Product Height US	4.03 in
------------------	---------	-------------------	---------

Technical Information

Operating Temperature Min	-40 °C	Phase	Single
Connection	Cable	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG

Operating Temperature	-40°-60°C	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized
-----------------------	-----------	--------------------------	---
