



Pass and Seymour
Turnlok® 67W48 Watertight Single Receptacle, Yellow
Part No. 67W48



Turnlok Watertight Single Receptacle, 20amp 250volt, NEMA Configuration L6-20, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007032963	Country Of Origin	United States
Features	Watertight	Application Sector	Industrial
Standard	UL Listed, CSA Listed	Warranty Type	1-Year
Type	Receptacle		

Dimensions

Product Width US	1.85 in	Product Depth US	4.03 in
Product Height US	1.85 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes		
Technical Information			
Operating Temperature Min	-40 °C	Connector Style	Locking
Flanged	No	Terminal Accommodation	#14 AWG - #10 AWG
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	20 A	IP Rating	IP67
Number of Poles	Double Pole	Indoor/Outdoor	Both
NEMA Configuration Code	L6-20R	Operating Temperature	-40°- 60°C
Number of Phases	1	Voltage	250.0 V
Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized		