

Single Receptacle 3-Pole 3-Wire 20A 125/250V



Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

For covering patents, see
www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007681017	Country Of Origin	Mexico
Number of Receptacles	1	Features	Durable
Outlet Type	Straight Blade	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 20
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.38 in	Product Depth US	1.15 in
Product Height US	1.75 in		

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	3-Way	Wire Size	14 - 12 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	10-20R
Voltage	125/250 V		
