



Pass and Seymour  
**Turnlok® 69W75 Watertight Single Receptacle, Yellow**  
Part No. 69W75



Turnlok Watertight Single Receptacle, 30amp 3 250 volt, NEMA Configuration L15-30, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

## Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|              |                       |                   |               |
|--------------|-----------------------|-------------------|---------------|
| Product Line | Pass & Seymour        | Color             | Yellow        |
| UPC Number   | 785007033359          | Country Of Origin | United States |
| Standard     | UL Listed, CSA Listed |                   |               |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.85 in | Product Depth US | 4.75 in |
| Product Height US | 1.85 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|            |     |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

### Technical Information

|                           |        |       |       |
|---------------------------|--------|-------|-------|
| Operating Temperature Min | -40 °C | Phase | Three |
|---------------------------|--------|-------|-------|

|                       |           |                           |                                                                                                                                                                                                                                                                     |
|-----------------------|-----------|---------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Number of Wires       | 4         | Operating Temperature Max | 60 °C                                                                                                                                                                                                                                                               |
| Amperage              | 30 A      | IP Rating                 | IP67                                                                                                                                                                                                                                                                |
| Number of Poles       | 3-Way     | Wire Size                 | 12 - 6 AWG                                                                                                                                                                                                                                                          |
| Operating Temperature | -40°-60°C | Environmental Conditions  | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only)<br>Flammability UL94V0 (boxes & wiring device interiors)<br>Operating Temperature - 40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |