

Turnlok Registered Receptacle 3-Pole 3-Wire 20A 125/250V



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007731002	Country Of Origin	Mexico
Number of Receptacles	1	Features	Impact Resistant
Application Sector	Industrial	Wall Plate Included	No
Standard	UL 498, FEDSPEC	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.437 in	Product Depth US	0.97 in
Product Height US	2.25 in		

Technical Information

Connection Location	Back and Side	Phase	Three
Number of Wires	3	Amperage	20 A
Number of Poles	3-Way	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	Wire Connection Type	Screw Terminals
Voltage	125/250 V		